


Axial kit EAMM-A-S48-70AA

Part number: 8105942

FESTO



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	12.5 Nm
Product weight	498 g
Interface code, actuator	S48
Interface code, motor in	70AA 70AB
Note on materials	RoHS-compliant