

Shock absorber DYSS-3-4-Y1F-G2

Part number: 8111390

FESTO



Data sheet

Feature	Value
Size	3
Stroke	4 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Max. impact velocity	1 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Single-acting Pushing
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Cushioning length	4 mm
Max. stop force	80 N
Max. tightening torque	1 Nm
Max. energy absorption per stroke	0.4 J
Max. energy absorption per hour	4500 J
Max. residual energy	0.004 J
Resetting force	0.5 N
Min. insertion force	3.5 N
Product weight	3 g
Load range	1 kg
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel
Piston rod material	High-alloy steel