


# Electronics module VMPA-MPM-EMM-P5

Part number: 8111881

FESTO



## Data sheet

Feature	Value
Max. no. of valve positions	1
Max. no. of solenoid coils	1
Reverse polarity protection	yes
DC load voltage operating voltage range	21.6 V...26.4 V
Nominal pick-up current per solenoid coil	60 mA to 30 ms
Nominal current with current reduction	22 mA after 30 ms
Electrical isolation between channel and internal bus	no
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-5 °C...50 °C
Product weight	20 g
Electrical actuation	Multi-pin
Housing material	POM
Note on materials	RoHS-compliant