

# Quick coupling EAMD-42-48-16-16X25

Part number: 8121126

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	16 mm
Diameter of holder 2	16 mm
Size	42
Nominal length	48 mm
Mounting position	Any
Max. rotational speed	6000 1/min
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	45 kgmm <sup>2</sup>
Transferable torque	17 Nm
Product weight	217 g
Note on materials	RoHS-compliant