

# Holder CAFM-D4-W

Part number: 8127358

FESTO



## Data sheet

Feature	Value
Width	216 mm
Height	97 mm
Length	345 mm
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 70 °C
Ambient temperature	0 ... 40 °C
Product weight	749 g
Mounting type	Threaded
Materials note	Conforms to RoHS
Material mounting bracket	steel, powder-coated