

Service unit MS6-EM1FR-1/2-D6-C-P-VC-A8-WPE-B

Part number: 8130911

★ Core product range

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Pressure gauge	Prepared for G1/8
Operating pressure MPa	0.1 ... 1 MPa
Working pressure	1 ... 10 bar
Standard flow rate exhaust 0.6->0 MPa (6->0 bar, 87->0 psi)	3,600 l/min
Standard nominal flow rate	4,750 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Compatibility with ester oil not guaranteed
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-5 ... 50 °C
Medium temperature	5 ... 50 °C
Ambient temperature	5 ... 50 °C
Product weight	1,250 g
Mounting type	Line installation With mounting bracket with accessories Optional
Materials note	Conforms to RoHS