

# Coupling EAMC-56-58-22-24

Part number: 8134826

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	22 mm
Diameter of holder 2	24 mm
Size	56
Nominal length	58 mm
Mounting position	Any
Max. rotational speed	5500 1/min
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	129 kgmm <sup>2</sup>
Transferable torque	60 Nm
Product weight	274 g
Note on materials	RoHS-compliant