

# Double nipple NPFC-DS-M5-G18-M

Part number: 8142591

FESTO



## Data sheet

| Feature   | Value   |
|---|---|
| Material threaded fitting                         | Nickel-plated brass                                     |
| Container size                                    | 10  |
| Working pressure                                  | -0.95 ... 10 bar  |
| Operating medium                                  | Compressed air in accordance with ISO8573-1:2010 [-:--] |
| Corrosion resistance classification CRC           | 1 - Low corrosion stress                                |
| PWIS conformity                                   | VDMA24364-B2-L  |
| Ambient temperature                               | -10 ... 60 °C   |
| Nominal tightening torque, pneumatic connection 1 | 10.55 Nm  |
| Nominal tightening torque, pneumatic connection 2 | 1.78 Nm   |
| Tolerance for nominal tightening torque           | ± 20 %  |
| Product weight                                    | 8.96 g  |
| Pneumatic connection, port 1                      | G1/8  |
| Pneumatic connection, port 2                      | M5  |
| Materials note                                    | Conforms to RoHS  |
| Material seals                                    | PVC   |