

# Reducing nipple NPFC-RS-G12-G38-MF

Part number: 8142598

FESTO



## Data sheet

Feature	Value
Material threaded fitting	Nickel-plated brass
Container size	10
Working pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Nominal tightening torque, pneumatic connection 1	47.9 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	22.84 g
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G3/8
Materials note	Conforms to RoHS
Material seals	PVC