


Parallel kit EAMM-U-145-D80-150A-188

Part number: 8157285

FESTO



Data sheet

Feature	Value
Size	145
Assembly position	Any
Gear unit ratio	1:1
Max. speed	4,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	2,259 kgmm ²
No-load driving torque	2 Nm
Transferable torque	50 Nm
Product weight	11,500 g
Interface code, actuator	D80B
Interface code, motor in	140A 150A
Materials note	Conforms to RoHS