

# Sub-base VMPA1-AP-4-EMG-D2-8-S

Part number: 8157740

FESTO



## Data sheet

Feature	Value
Width	42 mm
Length	107.3 mm
Width dimension	10.5 mm
Max. no. of valve positions	4
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure MPa	0.3 MPa...0.8 MPa
Pilot pressure	3 bar...8 bar
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Ambient temperature	-5 °C...50 °C
Product weight	180 g
Pneumatic connection 2	M7
Pneumatic connection 4	M7
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum