

Shock absorber DYSD-Q11-25-24-Y1F-Y9

Part number: 8161533

FESTO



Data sheet

Feature	Value
Size	25
Stroke	24 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Max. impact velocity	1 m/s
Reset time at room temperature	0.3 s
Mode of operation	Single-acting Pushing
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	24 mm
Max. stop force	4000 N
Max. energy absorption per stroke	140 J
Max. energy absorption per hour	150000 J
Max. residual energy	0.8 J
Resetting force	120 N
Min. insertion force	430 N
Product weight	635 g
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Steel, galvanized
Piston rod material	High-alloy steel
Nut material	Steel, galvanized