

Plastic tubing PU-3/8-SW

Part number: 8501

FESTO

For CN and CK connectors, particularly flexible and kink-resistant, polyurethane (not approved for use in the food industry).

This product is only available if ordered from the Festo Corporation, USA.

The maximum pressure value is permissible at the maximum temperature.



Data sheet

| Feature | Value |
|--|------------------|
| Outside diameter | 9.5 mm |
| Bending radius relevant for flow rate | 44 mm |
| Inside diameter | 6.5 mm |
| Temperature dependent working pressure | -0.95 ... 10 bar |
| Ambient temperature | -30 ... 60 °C |
| Product weight according to length | 0.048 kg/m |
| Color | Black |
| Materials note | Conforms to RoHS |