

Čep NPQE-P-S4-P10

Broj artikla: 8113204

FESTO



Tehnički podaci

Svojstvo	Vrijednost
Veličina	Standard
Položaj ugradnje	proizvoljno
Oblik	Blanking plug
Veličina pakiranja	10
Operating pressure for entire temperature range	-0,095 ... 0,8 MPa
Pogonski tlak kompletnog temperaturnog područja	-0,95 ... 8 bar
Operating pressure for entire temperature range	-13,775 ... 116 psi
Pogonski medij	Komprimirani zrak prema ISO 8573-1:2010 [7:4:4]
Uputa o mediju pogona i upravljanja	Moguć nauljeni pogon
Klasa korozione otpornosti KBK	1 - niska otpornost na koroziju
PWIS conformity	VDMA24364 zone III
Klasa čistog prostora	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-5 ... 60 °C
Težina proizvoda	0,35 g
Pneumatski priključak 1	Push-in sleeve diameter 4 mm
Boja, prsten za otpuštanje	plavo
Materijal - napomena	RoHS sukladno
Material housing	PBT
Material release ring	POM