

# Maitinimo kabelis KPWR-MC-1-SUB-9HC-5

Gaminio numeris: 537932

Nebetiekiamas produktas

[Tinka MTR-DCI-...](#)

FESTO



## Tech. Duomenys

Savybės	Reikšmė
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	Sub-D Mixed
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Nominalus DC įtampos lygis	24 ... 48 V
Kabelio ilgis	5 m
Kabelio priedas	tinkamas lanksčiai kabelio apsaugai
Bending radius, flexible cable installation	≥ 64 mm
Kabelio skersmuo	8,6 mm
Kabelio struktūra	2x1,5 Ekranuotas
Nominalus laidininko skerspjūvis	1,5 mm <sup>2</sup>
Laido galai	Pin terminal
Apsaugos klasė	IP54
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	0 ... 50 °C