



Variklio kabelis NEBM-M12G4-RS-2.23-N-M12G4H

Gaminio numeris: 571900

FESTO



Tech. Duomenys

Savybės	Reikšmė
Atitinka standartus	DIN 47100 EN 61984
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw locking with SW14
Electrical connection 2, function	Controller side
Electrical connection 2, design	apvalus
Electrical connection 2, connection type	Kištukas
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw locking with hexagonal SW18
Nominalus DC įtampos lygis	0 ... 250 V
Nominalus AC įtampos lygis	0 ... 250 V
Leistina srovės apkrova prie 40°C	4 A
Kabelio ilgis	2,23 m
Kabelio priedas	robotams
Bending radius, flexible cable installation	≥ 60 mm
Kabelio skersmuo	5,9 mm
Kabelio struktūra	4x0,34 Ekranuotas
Nominalus laidininko skerspjūvis	0,34 mm ²
Apsaugos klasė	IP67
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 80 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	0 ... 40 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	Juodas
Material housing	TPE-U(PUR)
Material seals	NBR
Material insulation	TPE-E