


Paskirstytojas

NEDU-L1R2-M12G5-M12LE-1R

Gaminio numeris: 8091516

FESTO



Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	EN 61076-2-101
Konstrukcija	Y-distributor with cable on controller side
Distributor type	1 to 2
Papildomos funkcijos	Additional supply for port B
Cable identification	Without inscription label holder
Prijungimo dažnis	100
Produkto svoris	72,5 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw-type lock with hex A/F 18 mm and longitudinal knurl
Electrical connection 2, function	Communication IO-Link
Electrical connection 2, design	apvalus
Electrical connection 2, connection type	Kištukas
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Electrical connection 2, type of mounting	Screw-type lock with hex A/F 13 mm and longitudinal knurl
Electrical connection 3, function	Papildomas maitinimo šaltinis
Electrical connection 3, connection type	2 single wires
Electrical connection 3, connection technology	atviri laidai
Electrical connection 3, number of pins/wires	2
Electrical connection 3, occupied pins/wires	2
Nominalus DC įtampos lygis	0 ... 30 V
Nominali darbinė nuolatinė įtampa	24 V
Leistina srovės apkrova prie 40°C	4 A
Atsparumas smūgiams	0,8 kV
Apsaugotas įžeminimas	Negalimas
Shielding	Ne
Kabelio ilgis	1 m
Cable length 1	1 m
Cable length 2	1 m
Kabelio priedas	Statiniam panaudojimui
Bending radius 1, fixed cable installation	≥ 11,7 mm
Bending radius 2, fixed cable installation	≥ 6 mm
Cable diameter 1	3,8 mm
Tolerance for cable diameter 1	± 0,1 mm
Cable diameter 2	1,75 mm
Tolerance for cable diameter 2	± 0,05 mm
Cable design 1	3x0,25

Savybės	Reikšmė
Cable design 2	2x0,5
Nominalus laidininko skerspjūvis	0,25 mm ² 0,5 mm ²
Apsaugos klasė	IP65 IP68 IP69K
Note on degree of protection	IP40 for socket M12 Sumontuotas
Aplinkos temperatūra	-30 ... 80 °C
Saugojimo temperatūra	-30 ... 80 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilkas
Material housing	PA TPE-U(PUR)
Korpuso spalva	Juodas
Material screw-type lock	Nickel-plated brass Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Nickel-plated and gold-plated bronze Brass, gold-plated
Material insulation	PVC