



Adapteris NEFM-REG6-K-0.5-B-R3G8

Gaminio numeris: 8097195

FESTO



Tech. Duomenys

Savybės	Reikšmė
Papildomos funkcijos	For battery
Produkto svoris	64 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	Connection pattern RE
Electrical connection 1, number of pins/wires	6
Electrical connection 1, occupied pins/wires	4
Electrical connection 2, function	Controller side
Electrical connection 2, design	kampinis
Electrical connection 2, connection type	Kištukas
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	RJ45
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	6
Nominalus DC įtampos lygis	0 ... 30 V
Nominalus AC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	1,6 A
Atsparumas smūgiams	2 kV
Shielding	Taip
Kabelio ilgis	0,5 m
Kabelio priedas	Standartas
Laido bandymo sąlygos	Bandymas pagal užklausimą
Bending radius, fixed cable installation	≥ 68 mm
Kabelio skersmuo	6,8 mm
Kabelio struktūra	4x(2x0,081)+(2x0,205)
Nominalus laidininko skerspjūvis	0,081 mm ² 0,205 mm ²
Nominal conductor cross section (AWG)	AWG24 AWG28
Apsaugos klasė	IP20
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-40 ... 80 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	0 - No corrosion stress
Material cable sheath	PVC
Kabelio apvalkalo spalva	Juodas
Material housing	PVC
Korpuso spalva	pilkas
Material insulation	PVC