

Set burduf EADB-V2-80-S201-300

Numar piesa: 1489408

FESTO



Fisa de date

| Caracteristica | Valoare |
|--------------------------------------|--|
| Ø exterior | 93 mm |
| Dimensiune | 80 |
| Gama de ridicare | 201 mm...300 mm |
| Prelungirea tijei de piston | 80 mm |
| Design | in jurul |
| Pozitie de instalare | orice |
| Structura constructiva | Burduf, set de montaj cu evacuare a aerului prin conducte |
| Clasa de rezistenta la coroziune KBK | 3 - stres intens de coroziune |
| Conformitatea LABS | VDMA24364-B2-L |
| Rezistenta la medii | Praf Aschii Uleiuri Grasime Benzina |
| Tip de protectie | IP65 conform IEC 60529 |
| Temperatura ambianta | -10 °C...80 °C |
| Masa in miscare | 168 g |
| Greutate produs | 365 g |
| Tipul de montare | deplasabil cu stift filetat |
| Conexiune pneumatica | G1/4 |
| Nota privind materialele | Conform RoHS |
| Material adaptoare | Aliaj de aluminiu forjat anodizat |
| Material garnituri | NBR |
| Material burduf | NBR |
| Material stift filetat | otel inoxidabil aliaj inalt |