

Cablu fibra optica SOEZ-LLG-SE-0,5-M4

Cod: 165357

FESTO



Fisa tehnica

Caracteristica	valoare
Metode de masurare	bariera luminoasa fibre optice
Temperatura mediului	-20 ... 160 °C
marime de fabricatie	M4
Greutate produs	46 g
Materialul carcasei	Alama cromat
Domeniu de reglare a limitei superioare	280 mm
Temperatura ambientala a instalatiei flexibile	-20 ... 120 °C
Tip de protectie	IP54
Conformitatea PWIS	VDMA24364-B2-L