

Teava plastic PQ-PA-12X1,5X3000

Numar piesa: 177728

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	12 mm
Ø interior	9 mm
Presiune de lucru in functie de temperatura	-0.95 bar...15 bar
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-25 °C...75 °C
Temperatura ambianta	-25 °C...75 °C
Greutatea produsului in functie de lungime	0.051 000015
Culoare	negru
Material furtun	PA