

# Suport ventuza vacuum ESH-HB-3-QS

Numar piesa: 189207

FESTO



## Fisa de date

Caracteristica	Valoare
Volum	0.519 cm <sup>3</sup>
Pozitie de instalare	vertical
Structura constructiva	Racord de vacuum lateral
Atribuirea suportului de ventuza	Dimensiune 3
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	0 °C...60 °C
Greutate produs	29 g
Tipul de montare	cu filet interior
Fixarea ventuzei	M4
Racord de vacuum	QS-6
Nota privind materialele	Conform RoHS
Material garnituri	NBR Otel
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt