

Suport ventuza vacuum ESH-HB-5-G

Numar piesa: 189211

FESTO



Fisa de date

Caracteristica	Valoare
Volum	1.921 cm ³
Pozitie de instalare	vertical
Structura constructiva	Racord de vacuum lateral
Atribuirea suportului de ventuza	Dimensiune 5
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	91 g
Tipul de montare	cu filet interior
Fixarea ventuzei	M10
Racord de vacuum	G1/8
Nota privind materialele	Conform RoHS
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt