

Suport ventuza vacuum ESH-HB-6-G

Numar piesa: 189212

FESTO



Fisa de date

Caracteristica	Valoare
Volum	7.25 cm ³
Pozitie de instalare	vertical
Structura constructiva	Racord de vacuum lateral
Atribuirea suportului de ventuza	Dimensiune 6
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	271 g
Tipul de montare	cu filet interior
Fixarea ventuzei	M20x2
Racord de vacuum	G1/4
Nota privind materialele	Conform RoHS
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt