

# Suport ventuza vacuum ESH-HD-5-G

Numar piesa: 189241

FESTO



## Fisa de date

Caracteristica	Valoare
Compensarea inaltimii suport de ventuza	10 mm
Volum	2.072 cm <sup>3</sup>
Pozitie de instalare	vertical
Structura constructiva	Racord de vacuum lateral cu compensarea inaltimii
Atribuirea suportului de ventuza	Dimensiune 5
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:-:-]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	195 g
Tipul de montare	cu piulita de blocare
Fixarea ventuzei	M10
Racord de vacuum	G1/8
Nota privind materialele	Conform RoHS
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt