


Ventuza vacuum fara conector ESV-20-BN

Numar piesa: 191054

FESTO



Fisa de date

Caracteristica	Valoare
Ventuza de compensare a inaltimii	6 mm
Raza min. a piesei de prelucrat	40 mm
Diametrul ventuzei	20 mm
Volum de aspiratie	1.6 cm ³
Pozitie de conectare	sus
Pozitie de instalare	orice
Forma de ventuza	burduf rotund de 1,5 ori
Presiune de lucru	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 000032...0 000032
Presiunea nominala de functionare	-70 kPa -0.7 bar -10.15 000032
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7::-]
Conformitatea LABS	VDMA24364-A1-L
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-10 °C...70 °C
Fora de mentinere la presiune de lucru nominala	12.9 N
Greutate produs	1.9 g
Culoare	negru
Duritate Shore	50 +/- 5
Nota privind materialele	Conform RoHS
Material ventuze	NBR