

# Garnitura luminoasa MF-LD-12-24DC

Numar piesa: 19143

FESTO



## Fisa de date

Caracteristica	Valoare
Indicatorul pozitiei de comutare	LED
Tipul de montare	pe ventil electromagnetic cu surub central M3
Greutate produs	1.6 g
Conector electric	Forma B design patrat MSF
Domeniu de tensiune de lucru CC	12 V...24 V
Conexiune conductor de protectie	disponibil
Putere nominala garnitura luminoasa	0.05 W
Tip de protectie	IP65
Temperatura ambianta	-25 °C...85 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	TPE-U (PU)
Culoare	transparent