

# Filtru-regulator LFR-1/2-D-5M-O-DI-MAXI-A

Numar piesa: 192389

FESTO



## Fisa de date

Caracteristica	Valoare
Dimensiune	Maxi
Seria	D
Blocaj de actionare	Buton rotativ cu blocare
Pozitie de instalare	vertical +/- 5°
Finete de filtrare	5 µm
Purjare a condensului	complet automat
Structura constructiva	filtru regulator fara manometru
Cantitate max. de condens	43 cm <sup>3</sup>
Protectie pahar	Cos metalic de protectie
Indicator de presiune	pregatit G1/4
Presiune de lucru	2 bar...12 bar
Domeniu de reglare a presiunii	0.5 bar...12 bar
Histerezis max. de presiune	0.4 bar
Debit nominal normal	4000 l/min
Medii de operare	Aer comprimat conform ISO 8573-1:2010 [7:9:-] Gaze inerte
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura de depozitare	-10 °C...60 °C
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [6:8:4] Gaze inerte
Temperatura medie	5 °C...60 °C
Temperatura ambianta	5 °C...60 °C
Greutate produs	1600 g
Tipul de montare	Instalarea liniei
Conector pneumatic 1	G1/2
Conexiune pneumatica 2	G1/2
Nota privind materialele	Conform RoHS
Material carcasa	Zinc turnat sub presiune PC