

Priza MSSD-C-S-M16

Numar piesa: 192748

FESTO



Fisa de date

| Caracteristica | Valoare |
|---|---|
| Frecventa de conectare | 10 |
| Tipul de montare | pe ventil electromagnetic cu surub central M3 |
| Pozitie de instalare | orice |
| Greutate produs | 38 g |
| Conector electric | 4 pini Priza Forma A |
| Diametrul cablului | 5.5 mm...8 mm |
| Sectiunea transversala nominala a conductorului | 0.5 000013...1 000013 |
| Tip de protectie | IP67 conform IEC 60529 |
| Temperatura ambianta | -25 °C...90 °C |
| Conformitatea LABS | VDMA24364-B2-L |
| Material carcasa | PA |
| Culoarea carcasei | negru |