

# Teava plastic PQ-PA-28X2,5X3000

Numar piesa: 194594

FESTO



## Fisa de date

Caracteristica	Valoare
Ø exterior	28 mm
Ø interior	23 mm
Presiune de lucru in functie de temperatura	-0.95 bar...10 bar
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-25 °C...75 °C
Temperatura ambianta	-25 °C...75 °C
Greutatea produsului in functie de lungime	0.204 000015
Culoare	negru
Material furtun	PA