

# Placa montare VN-T6-BP-NRH

Numar piesa: 196956

FESTO



## Fisa de date

| Caracteristica                       | Valoare                                      |
|--------------------------------------|--|
| Clasa de rezistenta la coroziune KBK | 2 - Solicitare moderata din cauza coroziunii |
| Conformitatea LABS                   | VDMA24364-B1/B2-L                            |
| Temperatura ambianta                 | 0 °C...60 °C                                 |
| Cuplu de strangere max.              | 0.8 Nm                                       |
| Greutate produs                      | 12.4 g                                       |
| Tipul de montare                     | cu orificiu de trecere<br>cu sina omega      |
| Nota privind materialele             | Conform RoHS                                 |
| Material placa                       | ranforsat cu PA                              |
| Material sertar                      | POM  |