

# Set burduf EADB-V2-50-S401-500

Numar piesa: 2828843

FESTO



## Fisa de date

Caracteristica	Valoare
Ø exterior	93 mm
Dimensiune	50
Gama de ridicare	401 mm...500 mm
Prelungirea tijei de piston	119 mm
Design	in jurul
Pozitie de instalare	orice
Structura constructiva	Burduf, set de montaj cu evacuare a aerului prin conducte
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B2-L
Rezistenta la medii	Praf Aschii Uleiuri Grasime Benzina
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	-10 °C...80 °C
Masa in miscare	305 g
Greutate produs	402 g
Tipul de montare	deplasabil cu stift filetat
Conexiune pneumatica	G1/4
Nota privind materialele	Conform RoHS
Material adaptoare	Aliaj de aluminiu forjat anodizat
Material garnituri	NBR
Material burduf	NBR
Material stift filetat	otel inoxidabil aliaj inalt