


Ventil pinch VZQA-C-M22C-15-GG-V2V4E-6

Numar piesa: 3412426

FESTO



Fisa de date

Caracteristica	Valoare
Structura constructiva	Ventil pinch actionat pneumatic
Tip de actionare	pneumatic
Principiul de etansare	slab
Pozitie de instalare	orice
Tipul de montare	Instalarea liniei
Conectare armatura	G1/2
Dimensiunea nominala DN	15
Functie de ventil	2/2 monostabil inchis
Directia de curgere	reversibil
Presiune mediu	0 MPa...0.6 MPa 0 bar...6 bar 0 000032...87 000032
Presiune de lucru	0.35 MPa...0.6 MPa 3.5 bar...6 bar 50.75 000032...87 000032
Presiune nominala armatura PN	10
Presiune de spargere	1.6 MPa 16 bar 232 000032
Tip de revenire	arc mecanic
Tipul de comanda	control extern
Conector aer auxiliar de control 12	M5
Mediu de comanda	Aer comprimat conform ISO 8573-1:2010 [7:4:1]
Mediu	Aer comprimat conform ISO 8573-1:2010 [-:~:1] Apa
Vascozitate max.	4000 mm ² /s
Temperatura medie	-5 °C...100 °C
Temperatura ambienta	-5 °C...60 °C

Caracteristica	Valoare
Temperatura de depozitare	5 °C...20 °C
Debit Kv	5 m3/h
Timp de comutare pornit	150 ms
Timp de comutare oprit	250 ms
Nota privind materialele	Conform RoHS
Conformitatea LABS	VDMA24364 zona III
Material carcasa	otel inoxidabil inalt aliat PA6
Cod material carcasa	1.4301
Material capac carcasa	otel inoxidabil aliaj inalt
Numar de material pentru capacul carcasei	1.4404 / AISI 316L
Material garnituri	FPM
Material element de blocare	EPDM
Greutate produs	537 g
Siguranta alimentara	vedeti informatii detaliate despre material