


Unitate ghidare FENG-80-250-KF

Numar piesa: 34525

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	80
Cursa	250 mm
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Forta max. Fy	2300 N
Forta max. Fy statica	3120 N
Forta max. Fz	2300 N
Forta max. Fz statica	3120 N
Moment max. Mx	170 Nm
Moment max. Mx static	231 Nm
Max. Moment My	191 Nm
Moment My static max.	259 Nm
Moment max. Mz	191 Nm
Moment Mz static max.	259 Nm
Forta de deplasare	40 N
Greutate produs	12355 g
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	Otel calit
Material carcasa	Aliaj de aluminiu forjat, anodizat
Material placa de jug	Otel calit