


Unitate ghidare FENG-100-400-KF

Numar piesa: 34535

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	100
Cursa	400 mm
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Forta max. Fy	2300 N
Forta max. Fy statica	3120 N
Forta max. Fz	2300 N
Forta max. Fz statica	3120 N
Moment max. Mx	198 Nm
Moment max. Mx static	268 Nm
Max. Moment My	197 Nm
Moment My static max.	267 Nm
Moment max. Mz	197 Nm
Moment Mz static max.	267 Nm
Forta de deplasare	40 N
Greutate produs	16070 g
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	Otel calit
Material carcasa	Aliaj de aluminiu forjat, anodizat
Material placa de jug	Otel calit