


Ventuza vacuum VAS-8-M5-NBR

Numar piesa: 34588

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	2 mm
Diametrul ventuzei	8 mm
Diametru de aspiratie eficient	5.5 mm
Pozitie de conectare	sus
Forma de ventuza	rotund plat
Presiune de lucru	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 000032...0 000032
Presiunea nominala de functionare	-0.07 MPa -0.7 bar -10.15 000032
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-20 °C...80 °C
Fora de smulgere la 70 % vacuum	1.6 N
Fora de mentinere la presiune de lucru nominala	1.6 N
Filet de fixare	M5
Fixarea ventuzei	M5
Racord de vacuum	M5
Culoare	negru
Duritate Shore	60 +/- 5
Material pivot de insurubare	Alama
Nota privind materialele	Conform RoHS
Material ventuze	NBR