

Ventuza vacuum VASB-75-1/4-NBR

Numar piesa: 35415

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	4 mm
Diametrul ventuzei	75 mm
Diametru de aspiratie eficient	60 mm
Pozitie de conectare	sus
Forma de ventuza	burduf rotund de 1,5 ori
Presiune de lucru	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 000032...0 000032
Presiunea nominala de functionare	-0.07 MPa -0.7 bar -10.15 000032
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-20 °C...80 °C
Fora de smulgere la 70 % vacuum	197 N
Fora de mentinere la presiune de lucru nominala	197 N
Filet de fixare	G1/4
Fixarea ventuzei	G 1/4
Racord de vacuum	G1/4
Culoare	negru
Duritate Shore	60 +/- 5
Material pivot de insurubare	Zinc turnat sub presiune
Nota privind materialele	Conform RoHS
Material ventuze	NBR