

Generator vacuum VAD-ME-3/8

Numar piesa: 35556

FESTO



Fisa de date

Caracteristica	Valoare
Diametru nominal duza Laval	2 mm
Pozitie de instalare	orice
Caracteristicile ejectorului	vid ridicat
Functie integrata	Ventil on/off electric
Structura constructiva	In forma de T
Presiune de lucru	1.5 bar...8 bar
Vacuum max.	85 %
Ciclu de lucru	100%
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Nota referitoare la mediul de lucru/comanda	Functionarea cu ulei nu este posibila
Conformitatea LABS	VDMA24364-B2-L
Temperatura medie	0 °C...40 °C
Tip de protectie	IP65
Temperatura ambianta	0 °C...40 °C
Greutate produs	242 g
Conector electric	Stecher
Tipul de montare	cu filet interior
Conector pneumatic 1	G1/4
Racord de vacuum	G3/8
Material carcasa	Aluminiu