



# Ventil cu buton T-5/3-1/4

Numar piesa: 4578

FESTO



## Fisa de date

Caracteristica	Valoare
Funcție de ventil	inchis 5/3
Tip de actionare	manual
Debit nominal normal	680 l/min
Racord pneumatic de lucru	G1/4
Presiune de lucru	0.2 MPa...1 MPa 2 bar...10 bar
Latimea nominala	7 mm
Principiul de etansare	slab
Tipul de comanda	pilotat
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	1160 g
Conector pneumatic 1	G1/4
Conexiune pneumatica 2	G1/4
Conector pneumatic 3	G1/4