


# Modul de ramificare MS6-FRM-1/4-Z

Cod: 529860

FESTO

Directia debitului de tranzit de la dreapta la stanga.



## Fisa tehnica

Caracteristica	valoare
pozitie instalare	oricare
structura constructiva	modul de ramificatie
presiune de operare	0 ... 20 bar
debit standard in directia principala de curgere 1->2	4.200 l/min
debit standard la iesirea superioara	6.000 l/min
debit standard la iesirea inferioara	6.400 l/min
mediu de operare	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
clasa de rezistenta la coroziune KBK	2
temperatura de depozitare	-10 ... 60 °C
temperatura mediului	-10 ... 60 °C -10 ... 60 °C
greutate produs	458 g
racord pneumatic 1	G1/4
racord pneumatic 2	G1/4
racord pneumatic 3	G1/2
racord pneumatic 4	G1/2
indicatie material	conform RoHS
informatii referitoare la material pentru carcasa	aluminu turnat sub presiune