


Combinatie filtre fine LFMBA-1-D-MAXI-DA

Numar piesa: 532872

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Maxi
Seria	D
Pozitie de instalare	vertical +/- 5°
Finete de filtrare	0.01 μm
Eficienta filtru	99.9999 %
Purjare a condensului	rotire manuala
Structura constructiva	Filtru de fibre
Cantitate max. de condens	80 ml
Protectie pahar	Cos metalic de protectie
Presiune de lucru	1 bar...16 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [6:8:4] Gaze inerte
Conformitatea LABS	VDMA24364-B1/B2-L
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [1:7:2] Gaze inerte
Temperatura medie	1.5 °C...60 °C
Continut de ulei rezidual	0.01 mg/m ³
Temperatura ambianta	-10 °C...60 °C
Greutate produs	2362 g
Tipul de montare	Instalarea liniei cu accesorii
Conector pneumatic 1	G1
Conexiune pneumatica 2	G1
Nota privind materialele	Conform RoHS
Material filtru	Fibra de borosilicat
Material carcasa	Zinc turnat sub presiune PC