


Combinatie filtre fine LFMBA-1/2-D-MIDI-DA-A

Numar piesa: 532878

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Midi
Seria	D
Pozitie de instalare	vertical +/- 5°
Finete de filtrare	0.01 μm
Eficienta filtru	99.9999 %
Purjare a condensului	complet automat
Structura constructiva	Filtru de fibre
Cantitate max. de condens	43 ml
Protectie pahar	Cos metalic de protectie
Presiune de lucru	1.5 bar...12 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [6:8:4] Gaze inerte
Conformitatea LABS	VDMA24364-B1/B2-L
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [1:7:2] Gaze inerte
Temperatura medie	1.5 °C...60 °C
Continut de ulei rezidual	0.01 mg/m ³
Temperatura ambianta	-10 °C...60 °C
Greutate produs	1429 g
Tipul de montare	Instalarea liniei cu accesorii
Conector pneumatic 1	G1/2
Conexiune pneumatica 2	G1/2
Nota privind materialele	Conform RoHS
Material filtru	Fibra de borosilicat
Material carcasa	Zinc turnat sub presiune PC