

Piulita olandeza MCK-PK-9-KD

Numar piesa: 533675

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Filet interior M16x1
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 000032...174 000032
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-10 °C...60 °C
Conector pneumatic 1	pentru niplu de legatura Ø interior 9 mm cu piulita olandeza
Material piulita olandeza	Aliaj de aluminiu forjat, placat cu nichel
Nota privind materialele	Conform RoHS