

Flansa oscilanta SNCL-12

Numar piesa: 537790

FESTO



Fisa de date

| Caracteristica | Valoare |
|--------------------------------------|--|
| Dimensiune | 12 |
| Pe baza standardului | ISO 21287 |
| Clasa de rezistenta la coroziune KBK | 2 - Solicitare moderata din cauza coroziunii |
| Conformitatea LABS | VDMA24364-B2-L |
| Temperatura ambianta | -40 °C...90 °C |
| Greutate produs | 20 g |
| Nota privind materialele | Conform RoHS |
| Material fixare | Aliaj de aluminiu forjat |
| Material rulment | Material plastic |
| Material suruburi | Otel galvanizat |