

Modul retea MS6-E-IPM-40-80

Numar piesa: 543496

FESTO



Fisa de date

Caracteristica	Valoare
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-10 °C...60 °C
Greutate produs	141 g
Nota privind materialele	Conform RoHS
Materialul placii de racordare	Aluminiu turnat sub presiune
Material garnituri	NBR
Material surub tubular	Aluminiu turnat sub presiune
Material conector module	Aluminiu turnat sub presiune
Material suruburi	Otel