


Regleta de conectare. VABM-B6-E-G14-5

Cod: 545816

FESTO

pentru electroventil VUVB.



Fisa tehnica

Caracteristica	valoare
marimea ramei	21 mm
numarul max. de pozitii de ventile	5
clasa de rezistenta la coroziune KBK	2
Moment de strangere max., montaj sina H	1,5 Nm
moment maxim de strangere la fixarea ventilului	2 Nm
Moment de strangere max., montaj perete	5 Nm
greutate produs	470 g
racord aer auxiliar de comanda 12/14	G1/8
racord pneumatic 1	G1/4
racord pneumatic 3	G1/4
indicatie material	Fara cupru si PFTE conform RoHS
Informatie material bara racordare	aliaj maleabil aluminiu