

Modul sursa de alimentare CDVI5.0-EB1X-MP-BI

Cod: 548431

FESTO



Fisa tehnica

Caracteristica	valoare
lungime	26,5 mm
numarul max. de pozitii de ventile	1
clasa de rezistenta la coroziune KBK	3
greutate produs	255 g
tip fixare	cu filet interior si bolt
racord pneumatic 1	G1/8
racord pneumatic 2	G1/8
racord pneumatic 3	G1/8
racord pneumatic 4	G1/8
racord pneumatic 5	G1/8
indicatie material	conform RoHS