

Set burduf DADB-V6-50-S351-375

Numar piesa: 553323

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	57 mm
Dimensiune	50
Gama de ridicare	351 mm...375 mm
Prelungirea tijei de piston	105 mm
Design	in jurul
Pozitie de instalare	orice
Structura constructiva	Burduf, set de montaj cu evacuare a aerului prin conducte
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B2-L
Rezistenta la medii	Praf Aschii Uleiuri Grasime Benzina
Tip de protectie	IP54
Temperatura ambianta	-10 °C...80 °C
Greutate produs	167 g
Tipul de montare	deplasabil cu stift filetat
Conexiune pneumatica	G1/4
Nota privind materialele	Conform RoHS
Material adaptoare	Ranforsat cu PA
Material garnituri	NBR
Material burduf	NBR
Material stift filetat	otel inoxidabil aliaj inalt