

Tub plastic PUN

Numar piesa: 553573

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	3 mm...16 mm
Ø interior	2 mm...11 mm
Presiune de lucru in functie de temperatura	-0.95 bar...30 bar
Autorizare	TÜV
Organizatia emitenta a certificatului	B 013277 0506 00
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B1/B2-L
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-35 °C...60 °C
Culoare	albastru maro galben verde natura rosu negru argintiu albastru translucid galben translucid verde translucid rosu translucid negru translucid alb
Nota privind materialele	Conform RoHS
Material furtun	TPE-U (PU)