

Tub plastic PLN

Numar piesa: 553850

FESTO



Fisa de date

| Caracteristica | Valoare |
|---|---|
| Ø exterior | 4 mm...16 mm |
| Ø interior | 2.9 mm...12 mm |
| Presiune de lucru in functie de temperatura | -0.95 bar...14 bar |
| Autorizare | TÜV |
| Organizatia emitenta a certificatului | B 013277 0506 00 |
| Mediu de operare | Aer comprimat conform ISO 8573-1:2010 [7:-:-] Apa conform declaratiei producatorului la www.festo.com |
| Conformitatea LABS | VDMA24364-B1/B2-L |
| Clasa de puritate a incaperii | Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1 |
| Siguranta alimentara | vedeti informatii detaliate despre material |
| Temperatura ambianta | -30 °C...80 °C |
| Culoare | albastru maro galben verde natura rosu negru argintiu alb |
| Nota privind materialele | Conform RoHS |
| Material furtun | PE |